



600ml Household Ultrasonic Cleaner , Ultrasonic Denture Cleaner For UV Paint

Our Product Introduction

Basic Information

- Place of Origin: China
- Brand Name: SKYMEN
- Certification: CE, FCC, RoHS
- Model Number: JP-890
- Price: Negotiation
- Delivery Time: In Stock



Product Specification

- Tank Material: SUS304(SUS316 Customized)
- Tank Size: L155*W95*H52mm
- Unit Size: L206*W152*H132mm
- Color: Blue, Grey
- Packing: 12PCS/carton
- Frequency: 42KHz
- Highlight: **ultrasonic vegetable cleaner,**
ultrasonic jewelry cleaner

for more products please visit us on skymenultrasonic.com

Product Description

600ml 42KHz Household Ultrasonic Cleaner For Denture Cleaning UV Paint

Features:

To cleaning ring ,earrings, necklace ,diamond
Timer setting: 0~30min, 18 cycles adjustable
Compact lid design to reduce the noise
Ultrasonic cleaning
UV paint, anti-scratch.
Certificate: CE & RoHS & FCC & ISO9001 2008

JP-890 specifications:

Tank capacity:600mL	Tank size:155×95×52mm
Ultrasonic power:35W	Unit size:206×152×132mm
Frequency:42KHz	Color box size:245×175×165mm
Timer:0-30min, 18 timer settings	Carton size:545×510×355mm
N.W.:0.9kg	Packing:12PCS/carton
G.W.:1.1kg	Color:Blue, grey



■ Product details

- ❶ Stainless steel sus304
- ❷ Transparent cover
- ❸ Digital display
- ❹ Adjustable timer
- ❺ Degas
- ❻ Watch holder
- ❼ Basket



■ Digital touch panel

- Electronic sensor
- Sensitive and durable



How to clean :


Cleaning guidance

1. Fill with clean water to mini level.
2. Add 3 drops professional cleaner.
3. Set time 3-5 minutes, put in the glasses to wash.



1. Fill with clean water to mini level.
2. Add 3 drops professional cleaner.
3. Set time 3-5 minutes, put in the watch on rack to wash, the watch must be water-proof.

1. Fill with clean water to mini level.
2. Add 3 drops professional cleaner.
3. set time 3-5 minutes, put in the jewellery to wash.



1. Fill with clean water to mini level.
2. Add 3 drops professional cleaner.
3. Set time 3-5 minutes, put in the razor head to wash.



Skymen Technology Corporation Limited

☎ 86-755-27094405

✉ info@skymen.cc

🌐 skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen