Our Product Introduction

0~30 Minutes Adjuable Benchtop Ultrasonic Cleaner 7L 180W For **PCB Electronic Parts**

Basic Information

. Place of Origin: China . Brand Name: Skymen

CE ROHS FCC SGS · Certification:

031S Model Number: • Minimum Order Quantity: 1 unit • Price: Negotiation · Packaging Details: 1unit per carton • Delivery Time: In Stock Payment Terms: T/T

. Supply Ability: 8000 pcs per month



Product Specification

031S Model: . Tank Capacity: 6.5L

• Internal Tank Size: 300x150x150mm(L X W X H)

180W Ultrasonic Power: 100W . Heating Power:

• Timer: 0~30 Minutes Adjuable

20~80°C Heater:

. Highlight: ultrasonic bath cleaner, table top ultrasonic cleaner



Product Description

7L Ultrasonic Cleaner 180W for PCB, Electronic parts, computer parts 40KHz

What are the advantages of ultrasonic over traditional cleaning methods?

Compared with traditional methods of ultrasonic cleaning allows you to:

- 1. Minimize the use of manual labor
- 2. Make cleaning and degreasing without the use of organic solvents
- 3. Clean hard to reach areas of products and remove all types of dirt
- 4. Shorten the processes such as extraction, dispersion, purification, chemical reactions
- 5. Eliminates costly mechanical and chemical cleaning of heat exchanger

Features

Every effective to clean cracks where hand can't reach.

With drainage

Fast delivery, it's in enough stock, you can receive it with 1 week after payment

The ultrasonic could come to hidden corner, zig zag passenge, give a throughout cleaning

Do no harm to any parts. Saving labor and cost;

Varies application for all metal parts, Such as other printer head, disel injector, PCB board, Jewelelry ,watch ,razor ,glass options

Stainless steel tank has resistance to wear and long work life.

Powerful industrial transducer output;

Can be used at home and factory.

031S product specification:

pp						
Model	031S					
Tank capacity	6.5L					
Internal tank size	300x150x150mm(L x W x H)					
Ultrasonic Power	180W					
Heating Power	100W					
Frequency	40KHz					
Timer	0~30 minutes adjuable					
Heater	20~80°C					

Images of this model:

Cleaning effect:













How to use?

- 1 Fill the tank with water
- 2 put the clieaning items into the tank
- 3 start the ultraosnics and set the temperature/cleaning time.

- Package Includes: 1 x Digital Ultrasonic Cleaner
- 1 x Cleaning Basket
- 1 x Manual

Application:

Auto part and machinery parts,

Lab and medical instruments;

Die casting and injection module;

All metal / plastic parts are suitable for ultrasonic cleaner .

A machine, a compact unit, for varies cleaning items!

What is ultrasonic cleaner?

Specially designed transducers transform electric energy into mechanical vibrations. These are transmitted into the cleaning liquid, creating many tiny vacuum-filled bubbles which rapidly implode. This process, called cavitation, releases highly energetic jets of liquid which remove all kinds of contamination from metal, glass, and plastic surfaces. Every surface that comes in contact with the fluid is thoroughly cleaned.

Other models for your choice

Mode	Tank size	Unit size	Volum	Ultrasonic	Ultrasonic	Heating	Time	Heating
□			е	power	frequency	power	r	temperature
į	L×W×H(mm)	L×W×H(mm)	(L)		(kHz)	(W)	(MIN)	(°C)
				(W)				
0105	150×135×100	175×160×210	2	60		100	1-30	0-80
)20S	240×135×100	265×165×220	3.2	120	╗	100	1-30	0-80
308	300×150×100	325×180×225	4.5	180	7	200	1-30	0-80
)31S	300×150×150	325×180×280	6.5	180	7	200	1-30	0-80
)40S	300×240×150	325×265×280	10.8	240	7	200	1-30	0-80
)60S	330×300×150	360×325×285	15	360	7	300	1-30	0-80
2080	500×300×150	530×325×285	22	480	40	500	1-30	0-80

100S	500×300×200	530×325x325	30	600	500	1-30	0-80

Free service of Skymen:
Free for inquiry before purchase, relevant information is available
Free experimentation of cleaning technology
Free equipment configuration and equipment installation

Free training for your technical and operational staff
Provide timely, efficient supply of spare parts accessories to all users.



Skymen Technology Corporation Limited



86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen