



30L Ultrasonic Cleaning Equipment 600W 40KHz For Lead Frame Capillary Tube Salver

Our Product Introduction

for more products please visit us on skymenultrasonic.com

Basic Information

- Place of Origin: Shenzhen, China
- Brand Name: SkyMen
- Certification: RoHS, CE, FCC, REACH
- Model Number: JP-100S
- Minimum Order Quantity: 1
- Price: Negotiation
- Packaging Details: Wooden case
- Delivery Time: In Stock
- Payment Terms: T/T
- Supply Ability: 8000 pcs per month



Product Specification

- Model: JP-100S
- First Tank Volume: 30L
- Tank Size: 500*300*200mm
- Ultrasonic Power: 600W
- Heating Power: 500W
- Frequency: 40KHz
- Timer: 0~30 Minutes Adjustable
- Temperature: 20~80°C Adjustable
- Highlight: Capillary Tube Ultrasonic Cleaning Equipment,
Lead Frame Ultrasonic Cleaning Equipment,
Salver Ultrasonic Bath Cleaner



More Images



Product Description

30L Ultrasonic Cleaner 600W for Lead frame / Capillary Tube / Salver 40KHz

Specification:

Model	JP-100S
Ultrasonic frequency	40,000Hz
Material of tank	SUS304
Material of shell	SUS304
Capacity	30L
Drain value	On the left side
Timer	0~30 mins adjustable
Temperature	20~80°C adjustable
Power supply type 1	AC 100~120V, 50/60Hz
Power supply type 2	AC 220~240V, 50/60Hz
Ultrasonic power	600W
Heating Power	500W
Tank inner dimension	500*300*200mm
Unit dimension	585*327*333mm
Packing size	680*455*400mmmm
N.W.	15kg
G.W.	17kg
Certificate	FCC & CE & RoHS & REACH


Similar models with different capacity:

Stainless Bench Top



Model	Capacity	Tank Size	Ultrasonic Power	Heating Power	Frequency
	(L)	(L*W*H)mm	(W)	(W)	(KHz)
008	0.8	150*85*65	35	0	40
009	0.9	150*135*65	60	100	40
JP-010T	2	150*165*100	60	100	40
JP-020S	3.2	240*135*100	120	100	40
JP-030S	4.5	300*150*100	180	200	40
JP-031S	6.5	300*150*150	180	200	40
JP-040S	10	300*240*150	240	200	40
JP-060S	15	330*300*150	360	300	40
JP-080S	22	500*300*150	480	500	40
JP-100S	30	500*300*200	600	500	40

Image:





COMPARISON OF CLEANING EFFECT



**Characteristics**

1. Use ordinary tap water, alcohol or solvent as cleaning solution
2. High-power transducer cleaning effect is significant, can be observed with the naked eye
3. After washing, the object shines brightly
4. Digital LCD control boot time
5. All stainless steel casing, inner liner and lid, even more upscale
6. The waterproof performance is greatly improved, and the product is safer and more durable.
7. With heating and temperature system
8. With handle and drainage system, it is more convenient

**Skymen Technology Corporation Limited**

86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen