

Shenzhen, China

JP-120S

Negotiation Wooden case

8000 pcs per month

In Stock

JP-120S

1

Auto Parts Ultrasonic Carburetor Cleaner, 38L Digital Ultrasonic Cleaner 40KHz

Basic Information

- Place of Origin:
- Brand Name:
- e: Skymen n: RoHS, CE, FCC, REACH
- Certification:
- Model Number:
- Minimum Order Quantity:
- Price:

Our Product Introduction

- Packaging Details:
- Delivery Time:
- Payment Terms: T/T
- Supply Ability:



Product Specification

- Model:
- First Tank Volume:
- Tank Size:
- Ultrasonic Power:
- Heating Power:
- Frequency:
- Time Setting:
- Temperature:
- Drain Value:
- Weight:
- Highlight:
- 38L 500*300*250mm 720W 800W 40KHz 0~30 Minutes Adjustable 20~80°C Adjustable In Right Side
- 20KG
- ultrasonic bath cleaner, table top ultrasonic cleaner



More Images



.

Product Description

Ultrasonic Cleaner for Auto Parts Carburator 38L with Heating Function Wide application of Ultrasonic Cleaner

1. Household applications: daily use items such as gold and silver jewelry, jewelry, headwear, brooches, glasses, bracelets, pens, discs, shavers, combs, toothbrushes, dentures, tea sets, etc. as well as bottles, teats and fruits such as grapes, cherry, Strawberries, these accessories, tools and fruits are disinfected while being cleaned. In addition, the hands can also be used for beauty skin care. Long-term use can keep the skin tender and smooth and full of elasticity. Jie Kang ultrasonic cleaner can also be used to mix wine, mellow wine, automatic stirring eggs and so on.

2. Eyeglasses and optical instruments: All optical lenses, such as various eyeglasses (including contact lenses), magnifying glasses, telescopes, microscopes, cameras, video cameras, and other lens parts, are cleaned by Jikang Ultrasonic, all the true feelings of the world are fully revealed.

3 Jade and ornament processing industry: During the process of grinding and polishing, a large amount of dust and dirt will adhere to jade and ornaments. These workpieces are often complex in shape and have many gaps. Traditional cleaning methods are often ineffective, and Jie Kang ultrasonic cleaning The device is unique and amazing.

4 Clocks, precision instruments: With Jie Kang ultrasonic cleaner, clocks and precision instruments eliminate the trouble of disassembling screws, gears, springs, springs and bracelets one by one. Just remove the shell and put the entire cleaning agent in it. (Such as gasoline) in the cleaning tank, you can get twice the result with half the effort.

5. Banks, offices, finance, arts and crafts, advertising industry, office supplies: such as printers, nozzles, stylus pens, pens, brushes, nozzles, sprayers are often blocked, and seals are often blurred due to the adhesion of printing ink. Jie Kang is commonly used Ultrasonic cleaner can keep smooth and clear. Such as the appropriate amount of detergent or other cleaning agents will have better results.

Specification:


Specification:				
Model	JP-120S			
Ultrasonic	40.000Hz			
frequency				
Material of tank	SUS304			
Material of shell	SUS304			
Capacity	30L			
Drain value	Yes			
Timer	0~30 mins adjustable			
Temperature	20~80°C adjustable			
Power supply type 1	AC 100~120V, 50/60Hz			
Power supply type 2	AC 220~240V, 50/60Hz			
Ultrasonic power	720W			
Heating Power	800W			
Tank inner dimension	500*300*250mm			
Unit dimension	585*347*385mm			
Packing size	680*455*450mm			
N.W.	19kg			
G.W.	20kg			
Certificate	FCC & CE & RoHS & REACH			

Similar models with different capacity:

Stainless Bench Top

Stanness Dench Top						
Model .	Capacity	Tank Size	Ultrasonic Power	Heating Power	Frequency	
	(L)	(L*W*H)mm	(W)	(W)	(KHz)	
008	0.8	150*85*65	35	0	40	
009	0.9	150*135*65	60	100	40	
010S	2	150*165*100	60	100	40	
JP-020S	3.2	240*135*100	120	100	40	
JP-030S	4.5	300*150*100	180	200	40	
JP-031S	6.5	300*150*150	180	200	40	
JP-040S	10	300*240*150	240	200	40	
JP-060S	15	330*300*150	360	300	40	
JP-080S	22	500*300*150	480	500	40	
JP-100S	30	500*300*200	600	500	40	
JP-120S	38	500*300*250	720	800	40	

Cleaning effect:



Certificate

Skymen passed Kmart inspected factory on 2015 taken by SGS, and Code of Conduct audit by Birgma, and each year factory audit taken by SGS,CE, ROHS, ISO9001:2008,FCC, C-Tick, Hi-New Technology Enterprise

