



40KHz Table Top Ultrasonic Cleaner 2 Liter 100W Heating Function For Lab Tools

Our Product Introduction

Basic Information

- Place of Origin: Shenzhen, China
- Brand Name: SkyMen
- Certification: RoHS, CE, FCC, REACH
- Model Number: JP-010
- Minimum Order Quantity: 1
- Price: Negotiation
- Packaging Details: Wooden case
- Delivery Time: In Stock
- Payment Terms: T/T
- Supply Ability: 8000 pcs per month



Product Specification

- Model: JP-010
- Tank Volume: 2L
- Tank Size: 150*135*100mm
- Ultrasonic Power: 60W
- Heating Power: 100W
- Frequency: 40KHz
- Time Control: 0~30 Minutes Adjustable
- Temperature: 20~80°C Adjustable
- Highlight: **ultrasonic bath cleaner, table top ultrasonic cleaner**

Product Description


Ultrasonic Cleaner 2 Liter for Lab Tools with 100W Heating Function

Advantages of ultrasonic cleaners:

1. Convenient and time saving, saving manpower and saving time.
2. The ultrasonic cleaning machine is designed with multiple safety devices, electric drive, no gas generation, and is environmentally friendly. With advanced technology and an experienced design team, the ultrasonic cleaner is able to clean a variety of printheads. Quality assurance CE and ISO9001.
3. With our own design and technology, our machines are designed to be highly efficient and clean, without damaging the cleaning components and for precise items.
4. We have our own independent technology research and development team as well as experienced design teams and skilled workers. We are able to offer the highest quality machines at the factory price.



Product Structure Display




Cooling device



SUS304 tank




Power switch/socket



Vents

JP-010 2.0L

ULTRASONIC POWER 60W




205mm
(8.0")



JP-020 3.2L

ULTRASONIC POWER 120W



230mm
(9.0")




JP-030 4.5L

ULTRASONIC POWER 180W




JP-031 6.5L

ULTRASONIC POWER 180W




JP-040 10L


ULTRASONIC POWER 240W



JP-060 15L


ULTRASONIC POWER 360W





JP-080 22L

ULTRASONIC POWER 480W



JP-100 30L

ULTRASONIC POWER 600W



PRODUCT FEATURES

1

mechanical timing:
The working time adjustable from 0-30 minutes or normal open mode.

2

mechanical control:
mechanical control heater, 20-80 adjustable, temperature error within ± 2

3

high quality bath:
High quality SUS 304 stainless steel punch forming bath with noise proof

4

anti-skid treatment:
the machine is steady with the non-slip, shock-proof, anti-static, pressure-proof mats at the bottom

5

ceramic heater:
New ceramic heater is stable and efficient

6

Humanized design, remarkable cleaning effect:
Tank capacity over 6L with the drain valve; high cleaning efficiency, no harm to surface

Suitable for varieties of places



Factory



Labs



Hardware store

JP-010 Specification:

| | |
|----------------------|----------------------|
| Ultrasonic frequency | 40,000Hz |
| Material of tank | SUS304 |
| Material of shell | SUS304 |
| Capacity | 2L |
| Timer | 0~30 mins adjustable |
| Temperature | 20~80°C adjustable |

| | |
|----------------------|--------------------------|
| Power supply type 1 | AC 100~120V, 50/60Hz |
| Power supply type 2 | AC 220~240V, 50/60Hz |
| Ultrasonic power | 60W |
| Heating Power | 100W |
| Tank inner dimension | 150*135*65mm |
| Unit dimension | 175*160*175mm |
| Inner Packing size | 255*240*230mm |
| Big carton for 12pcs | 525*500*485mm for 8pcs |
| N.W. | 2kg |
| G.W. | 2.5kg |
| Certificate | ISO9001:2008 & CE & RoHS |

Delivery

Usually we ship your cargo by FedEx, DHL, UPS or any other logistic company.

You can also use your own shipping agent.

RFQ

Q: What is your MOQ?

A:1 set.

Q: How to solve the equipment trouble during using ?

A: Please email us about problem with pictures or a small video will be better,we will find the problem and solve it. If broken, we will send you a new free part if in the warranty period.

Feedbacks

We value any comments, suggestions from you. If you got any problem, please contact us

Usually we ship your cargo by FedEx, DHL, UPS or any other logistic company.

You can also use your own shipping agent.

RFQ

Q: What is your MOQ?

A:1 set.

Q: How to solve the equipment trouble during using ?

A: Please email us about problem with pictures or a small video will be better,we will find the problem and solve it. If broken, we will send you a new free part if in the warranty period.

Feedbacks

We value any comments, suggestions from you. If you got any problem, please contact us



Skymen Technology Corporation Limited



86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen