

SUS304 1200ml Tank 70W Household Ultrasonic Cleaner For Jewelry

Basic Information

- Place of Origin:
- Brand Name:
- Certification:
- Model Number:
- Minimum Order Quantity:
- Price:
- Packaging Details:
- Delivery Time:
- Payment Terms:
- Supply Ability:

Guangdong China Skymen CE,FCC,ROHS,ISO JP-1200FT 24

Negotiation Packing size : 270*280*250 mm (L x W x H) 1pcs/ color box In Stock T/T, 5000000pcs/month



Product Specification

 Tank Material: 	SUS304	
 Tank Capacity: 	1200ml	
• Tank Size:	170 X 130 X 65 Mm (L X W X H)	
Unit Size:	228 X 218 X 157 Mm(L X W X H)	
 Frequency: 	40KHz	
• Power Supply:	AC100-120V/AC200-240V	
Product Name:	1200ml Jewelry Watch Glasses Cleaner Household Mini Ultrasonic Cleaner	
• Timer:	5 Interval Time Adjustable	
Ultrasonic Power:	70W	
Application:	Eyeglass Watch Jelwery,Cleaning Eyeglasses,watch,Lens	
 Highlight: 	1200ml Tank Household Ultrasonic Cleaner, 70W Household Ultrasonic Cleaner,	



More Images



SUS304 Tank Ultrasonic Jewelry Cleaner

Product Description

1200ml detachable tank household ultrasonic cleraner for jewelry eyeglasses watch fruit cleaning CE certification with timer

Specification:

technical parameter	Ultrasonic Frequency	40KHz
	Tank Material	Stainless Steel SUS304
	Tank Capacity	1200ML
	Timer	480 seconds auto stop,5 digital timer settings(90S,180S,280S,380S,480S)
	Heater	No
	Power Supply	AC 100 ~ 120V, 60Hz
		AC 220 ~ 240V, 50 Hz
	Ultrasonic power	70W
	Color	grey
Packing	Tank Size	170 x 130 x 65 mm (L x W x H)
	Unit Size	228 x 218 x 157 mm (L x W x H)
	Package Size	270*280*250 mm (L x W x H)
	Warranty	1 year

Product Discription:

Freatures:

1. with touch screen on the control panel, different from most ordinary press key design, easy to operate **Touch Key function:** Advanced international induction technology, avoid the damage of control panel and allow infinite repeated operation.

2. with a **detachable** stainless steel tank convenient for you to change water without the need to unplug the power cord every time,

--Also you can buy two tanks once for different objectives cleaning: one for fruits cleaning, one for jewby, eyeglasses, shaver, etc. cleaning.

---To save the space, you can install the machine on the wall; or put the tank on the desk.

- 3. Digital panel control,5 digital timer settings
- 4. With Degas
- 5. Small capacity, household ultrasonic cleaner
- 6.Includes basket,lid,holder and tweezers
- 7. Open the lid manually, transparent lid for more elegant looking
- 8. Isolated-circuit design keeps water away from circuit for enhanced safety
- 9. polished stainless steel tank is easy to clean
- 10. 40KHz ultrasonic frequency
- 11. compact lid design to reduce the noise

How does an ultrasonic cleaner work?

An ultrasonic system works by inducing controlled cavitation in the cleaning fluid. Cavitation refers to microscopic voids or 'bubbles' that form when the transducers emit sufficient ultrasonic energy into the fluid. The cavitation bubbles form relatively slowly and then collapse suddenly, releasing tremendous energy against the surfaces of objects immersed in the tank that 'scrubs' hard to remove soils from the parts.

No damage to the cleaned items.

Benefits of ultrasonic cleaning:

· Used for a wide range of workpiece shapes, sizes and materials


• The ultrasonic cleaning process gently moves parts to assist with cleaning; this mitigates the risk of damage to industrial parts during cleaning

· May not require the part to be disassembled prior to cleaning. Lower labor costs equal increased profits.

· Water, soap and green-friendly solvents are environmentally safe. Ultrasonic cleaning reduces/replaces hazardous cleaning solvents

· Short cycle times save time, money and increase plant efficiency









Our service:

1.Warranty:

12 months warranty for Skymen ultrasonic cleaner.

If any technical problem during warranty time, replacement parts will be sent free of charge.

Technical support is also available in whole time.

2.After-sales

Our machines undergo an extensive and strict testing and quality control procedure, ensuring every item purchased meet global quality standards.

♦Payment Methods♦

These payments of T/T,Western Union,Paypal are accepted. If you have any problem with the payment, please leave a message to us.

DHL, EMS and Fedex are our choices. If you prefer other reliable shipping company, please leave a message to us.

♦Tracking Number♦

Tracking number will be informed within 2-3 work days after delivery goods. If you have any problem with it, please leave a message to us. **Feedback**

Any comments, suggestions are accepted. We will be very grateful to your positive footprints left in our company. If you have any problem with our products, please leave a message to us.

♦Refund

Any damage or shortage of our goods after you receive your items, please take some photos for a witness. We will deal with it in 24 hours. Frequently, we will send a new part of items for heavy-damage. Before refund is accepted, please leave a message to us.



District, Shenzhen