

## 40KHz 120W 2500ml Household Ultrasonic Cleaner For Dental

Our Product Introduction

for more products please visit us on [skymenultrasonic.com](http://skymenultrasonic.com)

### Basic Information

- Place of Origin: Shenzhen China
- Brand Name: SkyMen
- Certification: FCC CE ROHS ISO9001 SGS
- Model Number: JP-2500T
- Minimum Order Quantity: 1pc
- Price: Negotiation
- Packaging Details: 1pcs/ color box; 4pcs / carton
- Delivery Time: In Stock
- Payment Terms: T/T
- Supply Ability: 50000000pcs/month



### Product Specification

- Tank Capacity: 2500ml
- Tank Materials: SUS304
- Ultrasonic Power: 120W
- Timer: 7 Interval Time Adjustable
- Tank Size: 250 X 150 X 80 Mm ( L X W X H )
- Frequency: 40KHz
- Power Supply: AC100-120V/AC220-240V
- Heating Power: 100W
- Highlight: 2500ml Household Ultrasonic Cleaner,  
120W Household Ultrasonic Cleaner,  
40KHz Stainless Steel Ultrasonic Cleaner



### More Images



## Product Description

### 2500ml big tank capacity household ultrasonic cleaner for dental

JP-2500T as a popular cleaning machine for dental clinic and jewelry store. The shell is made of environmentally-friendly high-strength ABS, with electrolytic polishing process of inner tank SUS304 stainless steel and using industrial-grade IC, high voltage isolation design, international brand power devices, the quality is stable and reliable.

#### Features:

1. With a stainless steel tank for convenience to do pouring and wiping
2. With Touch Screen on the control panel, different from most ordinary press key design
3. with both Weak and Strong cleaning mode for your choice to clean different objects
4. Cute appearance, colorful lid (2 colors optional)
5. Digital panel control, 0-3mins auto stop, 5 timer settings
6. Small capacity, household ultrasonic cleaner

#### 7. Auto shutoff

#### 8. Power High and normal settings

#### 9. Includes jewelry cleaner, basket, lid, holder.

#### 10. Open the lid manually

#### 11. 1 year warranty, and parts free to send for fix.

#### 12. FCC CE ROHS ISO9001 SGS certification

#### Specification:

<b>Model</b>	JP-2500	<b>Frequency</b>	40,000Hz
<b>Tank capacity</b>	2.5L	<b>Timer</b>	5 digital time setting
<b>Tank size</b>	248*150*78 mm	<b>Unit size</b>	290*223*185 mm
<b>Box packing</b>	360*270*245 mm	<b>Function</b>	Degasing/Power switch
<b>Ultrasonic power</b>	120W	<b>Heating power</b>	100W
<b>N.W.</b>	2.37kg	<b>G.W.</b>	2.9kg
<b>POWER SUPPLY</b>	AC 100 ~ 120V, 60Hz ; AC 220 ~ 240V, 50Hz		

1. Stringent production and aging process.
2. One-press heating up to temperature of 65°C.
3. High voltage isolation and humidity-proof and anti-corrosion treatment.

#### Products details:



## Production Display

- Front view of ultrasonic cleaner



- Side view of ultrasonic cleaner



•Other view of ultrasonic cleaner



## Product Details



1. Fashionable silver appearance, ABS environmental shell.
2. 304 stainless steel tank, corrosion-resistant, heat-resistant, safety and durability
3. With Transparent cover, the whole cleaning process is easy to be seen.
4. Convenient for changing plug and do maintenance.
5. Easy-to-open Cover
6. With cooling holes
7. With Silicone feet, non-slip and solid
8. Overflow port

## Power plug



Australian plug



UK plug



American plug



EU plug



## Product Advantage

- Large capacity



- Two industrial transducers



- constant temperature heating system



Packing:

1pcs/ color box; 4pcs / carton

Package Type:

Packing include

1ultrasonic cleaner

1 Power cord

1basket

1 English manuel

Industry	Description
Spectacles	Reading glasses, sunglasses, and small-size optical lens
Jewelry	Diamond, gold, silver and jade ware
Waist watch	Waterproof watch, and watch with metal band
Others/ household products	CD/ DVD disk, shaver cutter, nail cutter, pen, lock key, old coin, false tooth, and soup ladle
Commercial purpose	Appliances and tools of ophthalmology department or dental department, and jet nozzle of printer.

## FAQ:

### 1. How about after sales services?

1 Year warranty for Forall ultrasonic cleaner.

If any technical problem during warranty time, replacement parts will be sent free of charge. And technical support is also available after 1 year.

### 2. What are the advantages of ultrasound over traditional cleaning methods?

minimize the use of manual labor

make cleaning and degreasing without the use of organic solvents

clean hard to reach areas of products and remove all types of dirt

shorten the processes such as extraction, dispersion, purification, chemical reactions

eliminates costly mechanical and chemical cleaning of heat exchangers

### 3. What frequency is better for my parts?

Frequency is suggested based on pollutants in the objects.

28kHz frequency is stronger, better for car/motor/truck/vessel parts clean(remove oils, grease, pastes, etc. )

40kHz is better for pcb boards, electronic parts, etc.

Higher precision goods, higher frequency.

### 4. Can ultrasonic cleaning damage parts?

Ultrasonic cleaning is considered safe for most parts; although in some cases it is necessary to observe caution. Although the effect of thousands of implosions per second is very powerful, the cleaning process is safe.

### 5. What cleaning solution should I use?

A large variety of different formulas designed for specific applications. Proper selection is crucial for acceptable cleaning activity and to prevent unwanted reactions with the workpiece.



**Skymen Technology Corporation Limited**



86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen