




## Skymen Ultrasonic Bath For Electronic Cigarette With 200W Heater And Basket 2.85 Gallon

### Our Product Introduction

#### Basic Information

- Place of Origin: China
- Brand Name: Skymen
- Certification: CE ROHS FCC SGS
- Model Number: JP-040S
- Minimum Order Quantity: 1 unit
- Price: Negotiation
- Packaging Details: 1 unit per box
- Delivery Time: In Stock
- Supply Ability: 8000 pcs per month




#### Product Specification

- Model: JP-040S
- Frequency: 40KHz
- Capacity: 2.85 Gallon
- Tank Size: 12\*9\*6 Inch
- Ultrasonic Power: 120W/240W
- Heating Power: 200W
- Material: SUS 304
- G.W: 8.4KG
- Highlight: 30min Timer Ultrasonic Parts Cleaners, Bench Top Ultrasonic Cleaner SUS304, SUS304 Ultrasonic Cleaning Equipment



#### More Images



## Product Description

### Skymen Ultrasonic Bath For Electronic Cigarette With 200W Heater And Basket 2.85 Gallon

|                      |                                                       |
|----------------------|-------------------------------------------------------|
| Model                | <b>JP-040S</b>                                        |
| Ultrasonic Frequency | 40KHz                                                 |
| Transducer Quantity  | 4pcs                                                  |
| Ultrasonic Power     | 240W/120W                                             |
| Heating Power        | 200W                                                  |
| Tank Capacity        | 10.8L/2.85Gallon                                      |
| Tank Size            | 300*240*150mm                                         |
| Machine size         | 380*290*280mm                                         |
| Packing size         | 440*365*360mm                                         |
| Net weight           | 7.6KG                                                 |
| Gross weight         | 8.6KG                                                 |
| Time Range           | 1~30 minutes                                          |
| Temperature Range    | Room temperature~80°C/176°F                           |
| Tank material        | SUS 304                                               |
| Tank thickness       | 1mm                                                   |
| Shell material       | SUS 201                                               |
| Shell thickness      | 0.8mm                                                 |
| Slope panel degree   | 20°                                                   |
| Drain Valve          | ✓                                                     |
| General switch       | ✓                                                     |
| Degas                | ✓                                                     |
| Semi-wave            | ✓                                                     |
| Lid                  | ✓                                                     |
| Basket               | ✓                                                     |
| Voltage              | 110V; 220V                                            |
| Plug                 | European Plug; US plug; Austrslian Plug; British Plu  |
| Detergent suggestion | No stronger acid or alkali                            |
| OEM                  | Yes                                                   |
| OEM MOQ              | 50pcs                                                 |
| Origin               | Guangdong China                                       |
| Business category    | Manufacturer                                          |
| Lead time            | 7 days after payment if order quantity is below 20pcs |
| Payment term         | By cash; by credit card; by Paypal                    |
| Warranty             | 1 year                                                |

If you want choose other function, please see the buying guide as below:

1. Choose suitable tank size based on cleaning objects, size can be customized
2. Choose suitable frequency, 40kHz for common use and 28kHz for heavy duty oil removal
3. Choose tank material based on solvent, SUS304 or SUS316L
4. Other function optional, Ultrasonic cleaning tank + Ultrasonic Rinsing tank; Ultrasonic cleaning tank + Air agitation Rinsing tank; Ultrasonic cleaning tank + Water Rinsing tank; Ultrasonic cleaning tank + Hot air drying tank; Oil filtration system; detergent recycle use to save much cost.

**Stainless Bench Top**



| Model   | Capacity | Tank Size   | Ultrasonic Power | Heating Power | Frequency | Tank thickness | Material |
|---------|----------|-------------|------------------|---------------|-----------|----------------|----------|
|         | (L)      | (L*W*H)mm   | (W)              | (W)           | (KHz)     | (mm)           |          |
| JP-008  | 0.8      | 150*85*65   | 35               | 0             | 40        | 1              | SUS304   |
| JP-009  | 0.9      | 150*135*65  | 60               | 100           | 40        | 1              | SUS304   |
| JP-010T | 2        | 150*165*100 | 60               | 100           | 40        | 1              | SUS304   |
| JP-020S | 3.2      | 240*135*100 | 120              | 100           | 40        | 1              | SUS304   |
| JP-030S | 4.5      | 300*150*100 | 180              | 200           | 40        | 1              | SUS304   |
| JP-031S | 6.5      | 300*150*150 | 180              | 200           | 40        | 1              | SUS304   |
| JP-040S | 10       | 300*240*150 | 240              | 200           | 40        | 1              | SUS304   |
| JP-060S | 15       | 330*300*150 | 360              | 300           | 40        | 1              | SUS304   |
| JP-080S | 22       | 500*300*150 | 480              | 500           | 40        | 1              | SUS304   |
| JP-100S | 30       | 500*300*200 | 600              | 500           | 40        | 1              | SUS304   |

## PAY ATTENTION ON DETAILS



### Insulated handle design

Anti-static and anti-high temperature, more secure



### Stainless steel drain valve

One-half inch large drain valve, quicker to drain




### Cooling vents

Fast heat dissipation, protecting the circuit board and enhancing the service life




### Heat - resistant power cord

One-half inch large drain valve, quicker to drain



### Non-slip anti-shock pad

Non-slip, safer



### Safety switch

With ground insurance switch



### Stainless steel cleaning basket

Fine workmanship and durability



## HEATING SYSTEM

Built-in heating board, You can adjust the heating water temperature from 20 to 80°C. It's efficient to remove oil and wax


Heating board



## Product details

1./

Printed surface stainless steel  
fingerprint and dirt resisting



2./


SUS304 inner tank  
non-welded stamped tank  
features corrosion and heat  
resisting



### 3.

#### Heat emission design

heat emission holes at the bottom increase working life



### 4.

#### Drain valve

The drain valve is made of high quality copper, corrosion-resistant and switch adjustable



Water should not cover it



## New Upgrade And Tilted Touch Control Pannel

Angle of 20 degrees tilted,user-friendly



### JP-040S 10L Product Show

Heating power  
200W


Ultrasonic power  
240W

Transducer  
4 Pcs



## INDUSTRIAL TRANSDUSER

Strong cleaning resistance, good durability with powerful cleaning effect.



Frequency  
**40kHz**

Ultrasonic power  
**240W**

Transducer  
**4 Pcs**

## HEATING SYSTEM

Built-in heating board, You can adjust the heating water temperature from 20 to 80°C. It's efficient to remove oil and wax



Heating temperature  
**20-80°C**



Heating power  
**200W**




Application Area:

## MULTIPURPOSE CLEANING

It's efficient for most of household items that could be used to clean. get the best cleaning effects with the least effort.




Glasses



Watchband



Jewelry




Tableware



Toothbrush



Denture



Shaver



Bottles&nipples



Nail Tools





Before



After



Before




After




Before



After



Before



After



Before



After



Before



After



## COMPARISON OF CLEANING EFFECT





## Suitable for varieties of places



Factory



Labs



Hardware store



## PRODUCT FEATURES

- 1 mechanical timing:  
The working time adjustable from 0-30 minutes or normal open mode.
- 2 mechanical control:  
mechanical control heater, 20-80 adjustable, temperature error within  $\pm 2$
- 3 high quality bath:  
High quality SUS 304 stainless steel punch forming bath with noise proof
- 4 anti-skid treatment:  
the machine is steady with the non-slip, shock-proof, anti-static, pressure-proof mats at the bottom
- 5 ceramic heater:  
New ceramic heater is stable and efficient
- 6 Humanized design, remarkable cleaning effect:  
Tank capacity over 6L with the drain valve; high cleaning efficiency, no harm to surface

**Industrial Ultrasonic Cleaning Machine**



| Model     | Capacity<br>(L) | Tank Size<br>(L*W*H)mm | Transducers<br>(pcs) | Ultrasonic<br>Power<br>(W) | Heating Power<br>(W) | Tank thickness<br>(mm) | Frequency<br>(KHz) |
|-----------|-----------------|------------------------|----------------------|----------------------------|----------------------|------------------------|--------------------|
| JP-120ST  | 38              | 500X300X250            | 12                   | 600                        | 1500                 | 2                      | 28/40              |
| JP-180ST  | 53              | 500X350X300            | 18                   | 900                        | 1500                 | 2                      | 28/40              |
| JP-240ST  | 77              | 550X400X350            | 24                   | 1200                       | 3000                 | 2                      | 28/40              |
| JP-300ST  | 99              | 550X450X400            | 30                   | 1500                       | 3000                 | 2                      | 28/40              |
| JP-301ST  | 99              | 800X300X400            | 30                   | 1500                       | 3000                 | 2                      | 28/40              |
| JP-360ST  | 135             | 600X500X450            | 36                   | 1800                       | 4500                 | 2                      | 28/40              |
| JP-480ST  | 175             | 700X500X500            | 48                   | 2400                       | 6000                 | 2                      | 28/40              |
| JP-600ST  | 264             | 800X600X550            | 60                   | 3000                       | 6000                 | 2                      | 28/40              |
| JP-720ST  | 360             | 1000X600X600           | 72                   | 3600                       | 9000                 | 2                      | 28/40              |
| JP-1108ST | 540             | 1000X900X600           | 108                  | 5400                       | 18000                | 2                      | 28/40              |
| JP-1144ST | 960             | 1200X1000X800          | 144                  | 7200                       | 27000                | 2                      | 28/40              |

#### Immersible Transducer Plate

Image:



| Model    | Plate Size<br>(L*W*H)mm | Transducers<br>(pcs) | Ultrasonic Power<br>(W) | Generator<br>(set) | Suitable tank<br>(L) |
|----------|-------------------------|----------------------|-------------------------|--------------------|----------------------|
| JP-1006I | 305*205*100             | 6                    | 300                     | 1                  | 10~15                |
| JP-1012I | 355*305*100             | 12                   | 600                     | 1                  | 30~40                |
| JP-1018I | 340*280*100             | 18                   | 900                     | 1                  | 60~70                |
| JP-1024I | 430*280*100             | 24                   | 1200                    | 1                  | 70~80                |
| JP-1030I | 460*370*100             | 30                   | 1500                    | 1                  | 90~100               |
| JP-1036I | 550*450*100             | 36                   | 1800                    | 1                  | 130~140              |
| JP-1048I | 600*450*100             | 48                   | 2400                    | 2                  | 170~180              |

#### Immersible Transducer Tube

Image:



| Model   | Tube Size | Transducers | Ultrasonic Power | Generator | Length of wire |
|---------|-----------|-------------|------------------|-----------|----------------|
|         | (D*H)mm   | (pcs)       | (W)              | (set)     | (M)            |
| JM-1003 | 57*180    | 3           | 150              | 1         | 1.5            |
| JM-1006 | 57*300    | 6           | 300              | 1         | 1.5            |
| JM-1012 | 57*550    | 12          | 600              | 1         | 1.5            |
| JM-1018 | 57*750    | 18          | 900              | 1         | 1.5            |
| JM-1024 | 57*1000   | 24          | 1200             | 1         | 1.5            |
| JM-1036 | 57*1520   | 36          | 1800             | 1         |                |

Immersible Transducer Plate/tube can be put in any tank, but it doesn't have heating function.

The price of tube is much higher than plate, Ultrasonic Tube is only used for special purpose, such as in Lab.



**Skymen Technology Corporation Limited**



86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen