



## 1800W EMF SUS304L Ultrasonic Engine Cleaner 135L Skymen JP-360ST For Digital DPF

### Our Product Introduction

#### Basic Information

- Place of Origin: China
- Brand Name: Skymen
- Certification: CE, FCC, Rohs
- Model Number: JP-360ST
- Minimum Order Quantity: 1 unit
- Price: Negotiation
- Packaging Details: Wooden case packag size: 1120\*1460\*1070mm Wooden case
- Delivery Time: In Stock
- Payment Terms: T/T
- Supply Ability: 1000PCS/month



#### Product Specification

- Certification: CE, RoHS, CSA, FCC, EMF
- Material: Stainless Steel, SUS304L / SUS 316L
- Machine Type: Industrial Ultrasonic Cleaner
- Industry Used: Electronic Industry, Auto Industry
- Use: Container / Bottle Cleaning, engineer Parts Cleaning
- Condition: New
- Highlight: **SUS304L Ultrasonic Engine Cleaner, 1800W EMF Ultrasonic Engine Cleaner, 135L DPF Table Top Ultrasonic Cleaner**

## Product Description

### Skyemen Ultrasonic Cleaner JP-360ST 1800W 135L For Cleaning Digital DPF Industrial Motor Engine

#### FEATURES


1. stainless steel tank has resistance to wear and long work life.
2. tank capacity: 135 Liter, with Digital timer & heater control
3. with Stainless steel basket
4. Use just tap water, or industrial alcohol and solvent cleaner for more higher cleaning requirement
5. industrial control chip microcontroller. flexible circuit boards control, more secure & stable
6. with drainage, basket, lid and Multi-direction castors
7. Transducer : Korea technique
8. PCB board is independent research and development design production by skyemen
9. Generator is high quality technique designed and produced which have been used thousands of units by our USA and Europe customers.
10. circulation pump brand name: CNP (Famous brand)

#### Ultrasonic Cleaner's Specification

|                      |                         |
|----------------------|-------------------------|
| Ultrasonic Frequency | 40KHz                   |
| Material             | Stainless Steel SUS304  |
| Tank Capacity        | 135L                    |
| Transducer           | 36PCS                   |
| Timer                | 1-99minutes adjustable  |
| Heater               | 20°C to 95°C adjustable |

|                      |                             |  |
|----------------------|-----------------------------|--|
| Power Supply         | AC230V, 3 phase 50/60Hz,    |  |
|                      | AC380V, 3 phase 50/60Hz,    |  |
| Heating Power        | 4500W, Digital Heating      |  |
| Ultrasonic Power     | 1800W (40%-100% adjuatable) |  |
| Tank Size (LxWxH)    | 600*500*450mm               |  |
| Unit Size (LxWxH)    | 880*780*815mm               |  |
| Package Size (LxWxH) | 915x870x940mm (wooden case) |  |
| N.W./G.W.            | 98KG/120KG                  |  |
| Warranty             | 1 year                      |  |
| Customize Available  |                             |  |
|                      |                             |  |

## Product Process



### Similar models with different tank volume:

| Model            | Tank size     | Volume | Ultrasonic Power | Heating Power | Transducer |
|------------------|---------------|--------|------------------|---------------|------------|
|                  | L*W*H (mm)    | (L)    | (W)              | (W)           | (pcs)      |
| <b>JP-120ST</b>  | 500X300X250   | 38L    | 600W             | 1500W         | 12pcs      |
| <b>JP-180ST</b>  | 500X350X300   | 53L    | 900W             | 1500W         | 18pcs      |
| <b>JP-240ST</b>  | 550X400X350   | 77L    | 1200W            | 3000W         | 24pcs      |
| <b>JP-300ST</b>  | 550X450X400   | 99L    | 1500W            | 4500W         | 30pcs      |
| <b>JP-301ST</b>  | 800X300X400   | 96L    | 1500W            | 4500W         | 30pcs      |
| <b>JP-360ST</b>  | 600X500X450   | 135L   | 1800W            | 4500W         | 36pcs      |
| <b>JP-480ST</b>  | 700X500X500   | 175L   | 2400W            | 6000W         | 48pcs      |
| <b>JP-600ST</b>  | 800X600X550   | 246L   | 3000W            | 6000W         | 60pcs      |
| <b>JP-720ST</b>  | 1000X600X600  | 360L   | 3600W            | 9000W         | 72pcs      |
| <b>JP-1108ST</b> | 1000X900X600  | 540L   | 5400W            | 18000W        | 108pcs     |
| <b>JP-1144ST</b> | 1200X1000X800 | 960L   | 7200W            | 27000W        | 144pcs     |

### How to use an ultrasonic cleaner ?

Cleaning prior to lacquering

Ultrasonic clean 130° F, 2 to 3 minutes, 38 to 40 kHz sweep, 300 Hz sweep rate

Chemistry, Brulin 815GD, 12 ounces per gallon of water

Spray rinse with de-ionized\* water to remove gross detergent

Immersion rinse in flowing warm de-ionized\* water (30 seconds)

Spray rinse with de-ionized\* water (final rinse)

Blow dry with clean compressed air or dry nitrogen

Cleaning to remove calcium buildup (replaces "chem-clean")

Ultrasonic clean <110° F, 2 to 3 minutes, 38 to 40 kHz sweep, 300 Hz sweep rate

Chemistry, Ultra-power 132, 1 to 1½ ounces per gallon of water

Spray rinse with de-ionized\* water to remove gross detergent

Immersion rinse in flowing warm de-ionized\* water (30 seconds)

Spray rinse with de-ionized\* water (final rinse)

Blow dry with clean compressed air or dry nitrogen

Package by polywooden case:

Ultrasonic Cleaner's Cleaning Effect:

## CLEANING EFFECT

Better cleaning when cleaning with detergent



## Company Introduction

*We are the ultrasonic cleaner manufacturer and already in this industry for more than 13 years. We have two powerful factories, one located in Shenzhen and the other in Shaoguan to insure the production, also we have our professional engineer team for making a good cleaning plan for our customer.*

## Skymen Office



## Skymen Factory



## Skymen Exhibitions



## Skymen Activity



## FAQ

Q: What's the advantage of Skymen ultrasonic cleaner?

A: Skymen ultrasonic cleaner is the best way to have thorough cleaning without damaging objects. It helps to remove stubborn dirt and dust from the watch, eyeglasses, jewelry, etc, make them look new once again. It's very safe and easy to operate, proves to be the best helping hand for you at home.

Q: How often should I change the cleaning fluid in my tank?

A: Changed whenever it becomes visibly too contaminated, or when the cleaning process is not as effective.

Q: Why do I need to use a basket?

A: Basket would help to load objects together, and get a better cleaning effect.

Q: Can ultrasonic cleaning damage parts?

A: Although the effect of thousands of implosions per second is very powerful, the cleaning process is safe. No damage to your daily objects.

Q: What about the warranty?

A: 1 Year warranty for Skymen ultrasonic cleaner. If any technical problem during warranty time, replacement parts will be sent free of charge. And technical support is also available after 1 year.



**Skymen Technology Corporation Limited**



86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen