

240/480W Benchtop Ultrasonic Cleaning Machine 10L Surgical Instrument SUS304

Basic Information

- Place of Origin:
- Brand Name:
- Certification:
- Model Number:
- Minimum Order Quantity:
- Price:
- Packaging Details:
- Delivery Time:
- Payment Terms: T/T, L/C
- Supply Ability:



Product Specification

- Model:Frequency:
- JP-040PLUS 40KHz

300*240*150mm

China

1

SKYMEN

JP-040PLUS

Negotiation Carton

In Stock

CE/RoHS/ISO9001

3000pcs per month

- Dimensions:
- Material:
- Tank Thickness:
- Tank Capacity:
- Timer:
- Heater:
- Ultrasonic Power:
- Heating Power:
- Unit Size:
- Voltage:
- N.W/G.W:
- Package Size:
- Include:

2mm 10L 0-30min Adjustable Room Temp~80°C Adjustable 480/240W Switchable

Stainless Steel SUS304/SUS316

- 300W
- 345*293*310mm
- 110/220V
- N.W.6.6kg,G.W.7.4kg
-
- 435*360*385mm With Casters



Our Product Introduction

Product Description

Benchtop Commercial Parts Cleaning Machine Surgical Instrument Medical Ultrasonic Cleaner with Stronger Power 240/480W

Specification:

Model No.	JP-040S (Plus series)				
Image					
	Ultrasonic Frequency Material	40 kHz Stainless Steel SUS304			
	Tank Capacity	10L			
	Timer	1~99min adjustable			
Ultrasonic model	Heater	0°C to 80°C adjustable			
omasonic model	Power Supply	AC 100 ~ 120V, 50 / 60Hz			
	Fower Suppry	AC 220 ~ 240V, 50 / 60 Hz			
	Ultrasonic Power	480/240W			
	Heating Power	200 W			
	Basket& cover	Standard equiped			
	Tank Size	300*240*150mm(L x W x H)			
	Unit Size	345*293*310mm(L x W x H)			
Packing	Package Size	435*360*385mm(L x W x H)			
	N.W. / G.W.	N.W.8.9kg,G.W.9.9KG			
	Warranty	1 year			
Features.	 stainless steel tank has resistance to wear and long work life. with Digital timer & heater control, with stainless steel basket and cover. use just tab water, or industrial alcohol and solvent cleaner for more higher cleaning requirement ultrasonic cleaning solutions penetrate virtually any soil type includin oils, residues, solvents, pastes and chemicals and other contaminants are safely lifted and dispersed, leaving a surface appearance that is clean and free of particulate; even in crevasses and internal bores. 				
Application.	medical industry, electronic factory, molding factory, car workshop, diesel workshop, car industry, scientific laboratory, university lab, hardware tools shop.				
Certificates	CE/ROHS/FCC/PSE/I	SO9001			
Price(Not	USD \$240/pc, for sam USD \$220/pc, MOQ10 USD \$200/pc, MOQ80)pcs			

Our Product Introduction

Special Features:

- 1. stainless steel tank has resistance to wear and long work life.
- 2. tank capacity:10Liter

3.Use just tab water, or industrial

- alcohol and solvent cleaner for more higher cleaning requirement
- 4.industrial control chip microcontroller.flexible circuit boards
- control, more secure & stable
- 5.with drainage,basket,lid and Multi-direction castors
- 6. PCB board is independent research and development design production by skymen
- 7. It can applied to clean cast iron, steel, stainless steel, brass, bronze, and so on

Application:

-Scientific Labs:Eyeglass Frames;Lab Glassware;Optical&Contact Lenses;Pipettesscientific Instruments;Test tubes -Industrial Manufacturing:Assemblies;Gears;Metal&Plastic Parts;Precision Bearings -Electronic manufacturing:Capacitors;Ceramic Substrates;PC Boards;Packaging Components;Quartz Crystals -Medical and Dental Lab:Burs;Blood Oxygenators;Dental Instruments;Syringe Parts;Surgical Instruments -Jewelry Manufacturing:Chains;Charms;Coins;Intricate Settings;Precious Metals&Gemstones;Watches

If your company has other needs, you can choose the size that suits you according to the chart below

		Pa	aran	nete	ers		
Model							
	JP-020PLUS	JP-030PLUS	JP-031PLUS	JP-040PLUS	JP-060PLUS	JP-080PLUS	JP-100PLUS
Capacity (L)	3.2L	4.5L	6.5L	10L	15L	22L	30L
Tank Size (mm)	240*135*100	300*150*100	300*150*150	300*240*150	330*300*150	500*300*150	500*300*200
Overall Size (mm)	270*185*275	330*200*280	375*200*280	380*290*315	400*357*320	580*335*330	580*335*385
Ultrasonic Power	120W	180W	180W	240W	360W	480W	600W
Plus Ultrasonic Power	180W	300W	300W	480W	600W	840W	1080W
Heating Power	100W	200W	200W	200W	300W	500W	500W
Transducer Quantity	3pcs	5pcs	5pcs	8pcs	10pcs	14pcs	18pcs
Time Setting	1-99min						
Temperature Setting	up to 80°C						
With Drainage Tap	NO	NO	YES	YES	YES	YES	YES
With Cleaning Basket	YES						

How ultrasonic cleaner works:

Electrical energy is coverted into mechanical vibrations thanks to special elaborated transducers. These vibrations are transferred into the fluid through the walls of stainless steel. This creates tiny microscopic vacuum bubbles, which cause consecutive implosions (cavitation). The high-energy jets that are thus created can efficiently remove dirt from surfaces an materials placed in the cleaning bath.

An ultrasonic cleaner in your kitchen will save time and reduce effort while providing a safe solution for your kitcheware. With the help of oil remove detergent the ultrasonic cleaner could fast and efficient take the oil polish the kitcheware. when using an ultrasonic cleaner on glassware, plasticware, and your lab instruments. Whether you are cleaning **oven trays**, **pans.** studies have shown that it can be up to 30 times faster while delivering thoroughly clean results

Company profile

Here are the Skymen company. You can know more about us with the details.

Statmen	skymen v	I Wer
Skymen ubresonic , which is a leading manufacture for more than 1.Syears. The	Ultrasonic Cleaner M and national high-tech enterprise.van founded in 2007.We have been focusing on R a an more than 200 parters & certificates in total. Cur products range covers house top strasonic Ceener, industrial ultrasonic cleaner, castoniand-ultrasoric cleaner e	60 of ultrasonic equipment & cleaning solution vide ultrasonic cleaner,
2007	2009	2012
SET UP Skymen Cleaning Equipment Shenzhen Co., Ltd. was founded in 2007.	DEVELOP In 2009, Skymen established a branch in HongKong and a factory in Shenzhen.	OPTIMIZE Added mold injection and Delis department, which focus on R & D and manufacturing.
2016	2017	2021
CERTIFICATION Through High-tech Enterprise Certificate, ISO 9001 certification and Medical device registration certification.	EXPANSION In Fuyong to set up a new marketing center, in Gongming to set up a manufacturing center.	TAKE OFF Newly build Shaoguan Industrial Park, vigorously R&D laboratories and ultrasonic cleaning technology.

SKYMEN

Industrial Ultrasonic Cleaning Machine



Cleaning Rinsing Drying Filtering Bubbling Lifting Agitation



FAQ:

May I ask which Optical glass can use ultrasonic cleaners?

Lens, prism, spectacle frame, precious metal decoration, optical fiber, liquid crystal LCD, TF

What are the benefits of using ultrasonic cleaners?

1. Clean integration

When using a medical ultrasonic cleaning machine, it is necessary to manually put in medical utensils and cleaning fluid, but after the cleaning machine is turned on, it can be cleaned intelligently and integratedly.

2. Protect the health and safety of medical personnel

Scalpels, glass slides, tweezers, etc. are inevitably sharp in medical equipment. If the equipment is stained with patient's blood, there will inevitably be the possibility of infection during manual cleaning. The use of medical ultrasonic cleaners can avoid manual cleaning and infection.

3. Better cleaning effect

Once the medicines or blood stains on the medical equipment are dry, it is difficult to clean it by hand. Even if there are no stains on the surface, there will still be stubborn bacteria residues. The medical ultrasonic cleaner can produce a large amount in the cleaning solution when it is started. The tiny air bubbles that impact the medical appliance can also penetrate deep into the many gaps of the appliance. The cleaning effect produced by this ultrasonic cavitation is irreplaceable manually, and the medical appliance can be cleaned more thoroughly.

How about after sales services?

12 months warranty for SKYMEN ultrasonic cleaner. Any technical problem during warranty time, free replacement parts will be sent to your door. And technical support is also available after 1 year.

What are advantages of ultrasound over traditional cleaning methods?

1). minimizes the use of manual labor

- 2). makes cleaning and degreasing without the use of organic solvents
- 3). reaches every area of product and remove all types of dirt
- 4). shorten processes such as extraction, dispersion, purification, and chemical reactions.
- 5). eliminates costly mechanical and chemical cleaning of heat exchangers
- How long will the order take to make?

Under regular production capacity, it takes 25 days after your confirmation of details.

Skymen Technology Corporation Limited					
Q	86-755-27094405	O i	nfo@skymen.cc	e	skymenultrasonic.com
Floor 1st & 2nd, Bu	uilding 3, Tanggang Ta		dustrial Park, Da istrict, Shenzhen		an Community, Shajing Street, Bao'an