



JP-520 200ml Ultrasonic Dental Instrument Cleaner AC 220-240V One Click For Homeuse

Our Product Introduction

for more products please visit us on skymenultrasonic.com

Basic Information

- Place of Origin: China
- Brand Name: Skymen
- Certification: CE/ROHS/FCC/ISO9001
- Model Number: JP-520
- Minimum Order Quantity: 1 sets
- Price: Negotiation
- Packaging Details: carton box
- Delivery Time: In Stock
- Payment Terms: L/C, T/T, Paypal
- Supply Ability: 5000sets per day



Product Specification

- Material: ABS
- Clean Medium: Wet Cleaning
- Theory: Physical Cleaning
- Character: Thorough Cleaning
- Control Mode: Artificial
- Customize: Available
- Status: New
- Ultrasonic Power: 25W
- Ultrasonic Frequency: 40kHz
- Inner Tank Size: 90*72*31.5mm
- Unit Size: 100*76*40mm
- Box Size: 141*95*68mm
- Capacity: 200ml
- Highlight: 200ml Ultrasonic Dental Instrument Cleaner, Ultrasonic Dental Instrument Cleaner 25W, One Click Dental Instrument Ultrasonic Cleaner



More Images



Product Description

wholesale ultrasonic cleaner JP-520 200ml from SKYMEN for dental instrument washing

This machine is great for homeuse, excellent for cleaning jewellery, Precise Barrels ect.

Specification:

Model	JP-520
Ultrasonic power	25W (1pc transducer)
Frequency	40KHz
Housing material	ABS
Tank material	SUS304
Tank capacity	0.2L /10oz
Timer	One-click cleaning
Voltage	AC 100~120V, 60Hz AC 220~240V, 50Hz
Tank size	90*72*31.5mm
Unit size	100*76*40mm
Packing size	141*95*68mm
N.W.	0.45Kg
G.W.	0.55Kg
Certificate	ISO9001:2008;CE; RoHS;FCC

Features:

1. Resistance to wear and long work life.

2. Tank capacity: 0.5L, with digital timer .
3. With basket and lid, UM
4. Use just tap water, or industrial alcohol and solvent cleaner for more higher cleaning requirement
5. Flexible circuit boards control, more secure & stable
6. Certification: CE & RoHS & ISO9001

Application Field			
Scientific Labs	Eyeglass Frames Lab Glassware Optical & Contact Lenses Pipettes Scientific Instruments Test Tubes	Industrial Manufacturing	Assemblies Gears Metal & Plastic Parts Precision Bearings Relays & Motors Switches Precise Barrels gun parts Tungsten Steel Tip Darts
Electronics Manufacturing	Capacitors Ceramic Substrates PC Boards Packaging Components Quartz Crystals SMDs	Medical & Dental Lab	Burs Blood Oxygenators Cannulae Dental Instruments Syringe Parts Surgical Instruments
Jewelry Manufacturing	Chains Charms Coins Intricate Settings Precious Metals & Gemstones Watches	Auto Industry	Carburetor Castings Fuel Injectors Machined Parts Stamped Parts Switches



1.Raw Material Inspection:

QC and engineers would make strict inspection of the raw material step by step to ensure quality product.

2.Sales checking:

We salesman would also check the production process to ensure machine 100% according to the sample

3.100% product inspection:

100% products checking during production, Standard unit would be under testing at least 4hours, customized machine will test at least 2 days before delivery.

4.We always try to do perfect:

Everyone in Skymen would try best to solve problems together with you.

FAQ**Could I Get one sample of the Ultrasonic Cleaner?**

Yes, sample orders welcomed. Sample details please contact with saler. If need customized, Silk printing time is 3-7 days, hot transfer time is 10 days.

2. Do you have your ownfactory?

Yes, we have OEM products and professional for plastic nealy 20 years.

3. Could I use my ownlogo or design on the Ultrasonic Cleaner?

Yes, Customized logo and design on mass production are available. And you can choose the colors or materials.

4. What is thedelivery time of the Ultrasonic Cleaner?

Standard samples are available! 15-30 days for mass production after you confirm the samples all the details

5. Which kinds ofcertificate would your Ultrasonic Cleaner have?

CE ROHS FCC REACH ISO13485 ISO9001 SGS, BPA, LFGB, etc.



Sky men Technology Corporation Limited



86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen