




Authorized
Online Agent

SkyMen Technology Corporation Limited
skymenultrasonic.com



Large Double Tanks Industrial Ultrasonic Cleaning Machine Rinsing Ultrasonic Cleaner for Oil Degrease 77L

Our Product Introduction

for more products please visit us on skymenultrasonic.com

Basic Information

- Certification: CE, RoHS, ISO9001
- Minimum Order Quantity: 1
- Price: 2880



Product Specification

- Ultrasonic Power: 1.2kw
- Tank Capacity: 77L For Each
- Voltage: 380V 3phases
- Material: Stainless Steel SUS304
- Tank Thickness: 2mm
- Timer: 1-99 Hours Adjustable
- Unit Size: 1450*1050*760mm
- G.W: 220kg
- Heating Power: 3000W
- Package Size: 1510*1110*880mm
- Frequency: 28/40kHz
- Heater: 20-95
- Ultrasonic Frequency: 28/40 KHz
- Tank Size: 550*400*350mm
- Power Supply: AC 100 ~ 120V, 50 / 60Hz, AC 220 ~ 240V,



More Images



Product Description

Large Double Tanks Industrial Ultrasonic Cleaning Machine Rinsing Ultrasonic Cleaner For Oil Degrease 99L

1 Model No.

JP-2048G

2 Image

3 Ultrasonic model	Ultrasonic Frequency	28/40 kHz
	Material	Stainless Steel SUS304
	Tank Capacity	77L for each
	Timer	1~99hours adjustable
	Heater	20°C to 95°C adjustable
	Degas	Yes
	Semiwave	Yes
	Power Supply	AC 100 ~ 120V, 50 / 60Hz AC 220 ~ 240V, 50 / 60 Hz
	Ultrasonic Power	0-1200 W
	Heating Power	3000W*2
	Basket& cover	Standard equipped
	Tank Size	550*400*350mm (L x W x H)
	Unit Size	1450*1050*760mm (L x W x H)
4 Packing	Package Size	1510*1110*880mm(L*W*H)
	G.W.	220 kg
	Warranty	1 year

- 5 Features.
1. stainless steel tank has resistance to wear and long work life.
 2. with filtration and rinsing system,
 3. with stainless steel basket and cover.
 4. use just tap water, or industrial alcohol and solvent cleaner for more higher cleaning requirement
 5. ultrasonic cleaning solutions penetrate virtually any soil type including: oils, residues, solvents, pastes and chemicals and other contaminants are safely lifted and dispersed, leaving a surface appearance that is clean and free of particulate; even in crevasses and internal bores.

- 6 Application medical industry, electronic factory, molding factory, car workshop, diesel workshop, car industry, scientific laboratory, university lab, hardware tools shop.

7 Certificates CE/ROHS/FCC/PSE/ISO9001

Ultrasonic machine Features:

Twin tank ultrasonic cleaner ,1 for cleanig ,1 for rinsing ,to achive better result.

Adjustable ultrasonic power from 300W to 30KW or even bigger

Original BLT type transducer with more strong power

SUS304 or 316L stainless steel tank for solvent fluid cleaning

With bolted transducer or whole set transducer pack system

Adjustable thermo controller

With separate control ultrasonic electronic generator

Ultrasonic tank size can be custom made

An ultrasonic carburetor cleaner cleans even gummed up carburetors. Stop wasting time hand cleaning.

Fast and effective cleaning with no manual labor

Powerful enough to remove carbon deposits yet gentle on aluminum parts

Use water-based cleaning solutions, no toxic solvents

Application:

-Scientific Labs: Eyeglass Frames; Lab Glassware; Optical&Contact Lenses; Pipettes; scientific Instruments; Test tubes

-Industrial Manufacturing: Assemblies; Gears; Metal&Plastic Parts; Precision Bearings

-Electronic manufacturing: Capacitors; Ceramic Substrates; PC Boards; Packaging Components; Quartz Crystals

-Medical and Dental Lab: Burs; Blood Oxygenators; Dental Instruments; Syringe Parts; Surgical Instruments

-Jewelry Manufacturing: Chains; Charms; Coins; Intricate Settings; Precious Metals&Gemstones; Watches

How ultrasonic cleaner works:

Electrical energy is converted into mechanical vibrations thanks to special elaborated transducers. These vibrations are transferred into the fluid through the walls of stainless steel. This creates tiny microscopic vacuum bubbles, which cause consecutive implosions (cavitation). The high-energy jets that are thus created can efficiently remove dirt from surfaces and materials placed in the cleaning bath.

An ultrasonic cleaner in your kitchen will save time and reduce effort while providing a safe solution for your kitchenware. With the help of oil remove detergent, the ultrasonic cleaner could fast and efficient take the oil, polish the kitchenware. When using an ultrasonic cleaner on glassware, plasticware, and your lab instruments. Whether you are cleaning **oven trays, pans**, studies have shown that it can be up to 30 times faster while delivering thoroughly clean results

Company profile

Here are the Skyman company. You can know more about us with the details.

FAQ:

Q: What frequency is better for my parts

A: Frequency is suggested based on pollutants in the objects.

28kHz frequency is stronger, better for car/motor/truckessel parts clean (remove oils, grease, pastes, etc.)

40kHz is better for pcb boards, electronic parts, etc.

Higher precision goods, higher frequency.

Q: Can ultrasonic cleaning damage parts? A: Although the effect of thousands of implosions per second is very powerful, the cleaning process is safe. No damage to your daily objects.

Q: What cleaning solution should I use? A: A large variety of different formulas designed for specific applications. Proper selection is crucial for acceptable cleaning activity and to prevent unwanted reactions with the workpiece.

Q: Is rinsing after cleaning cycles? A: Rinsing is recommended to remove any chemical residue that could be harmful to the part. Details can be rinsed right in your ultrasonic cleaner or in a clean water bath or in a separate sink tap, distilled or deionized water

Ultrasonic cleaning tank + Air agitation Rinsing tank

Ultrasonic cleaning tank + Water Rinsing tank

Ultrasonic cleaning tank + Hot air drying tank

Oil filtration system: detergent recycle use to save much cost



Skyman Technology Corporation Limited



+86 13528763370



sales3@skyman.cc



skymanultrasonic.com