

## New design 15L 40KHz fast cleaning digital ultrasonic cleaner with degas function

Our Product Introduction

for more products please visit us on [skymenultrasonic.com](http://skymenultrasonic.com)

### Basic Information

- Place of Origin: ShenZhen
- Brand Name: SkyMen
- Certification: CE,RHOS
- Model Number: JP-060S
- Minimum Order Quantity: 1set
- Price: Negotiation
- Packaging Details: 1pcs / carton 1x ultrasonic cleaner 1x basket 1x lid 1x user manual
- Delivery Time: In Stock
- Payment Terms: T/T, Paypal
- Supply Ability: 500sets



### Product Specification

- Model: JP-060S
- Tank Capacity: 15L
- Tank Size: 330\*300\*150mm
- Unit Size: 387\*325\*280mm
- Package Size: 460\*410\*360 Mm
- Frequency: 40KHz
- Power: 120/240W
- Heating Power: 300W
- Heater: Normal ~80C Adjustable
- Timer: 1~30min Adjustable
- Warranty Time: 1 Year
- Lead Time: Immediately After Payment
- Highlight: **table top ultrasonic cleaner, ultrasonic cleaning equipments**



### More Images



## Product Description

### 15L Fast Cleaning Digital Ultrasonic Cleaner With Degas Function For Oily Parts

#### 1.Degas Function

The key factor of ultrasonic cleaning effect is the cavitation caused by ultrasonic wave among the liquid. If there is air or other gas in water, it will reduce cavitation in liquid. Degas function is designed for solving this problem to improve cleaning effect. Besides, it will reduce some oxidation on metal material.

#### 2.Application

Using in all kinds of spare parts cleaning including brass component, medical instrument, industrial parts and etc.

Application Chart

<b>ELECTRONICS / ELECTRICALS</b> PCB's Electronic assemblies, Opto - Electronics, Glass substrates, Switchgear, Armature	<b>WATCH AND JEWELLERY</b> Clock / Time Piece, Watches, Metal straps, Watch Cases, Jewellery Imitation Jewellery, Diamonds and other precious articles	<b>PHARMACEUTICALS</b> Degassing of solvents before HPLC, Dissolution / Disintegration of sugar coated tablets, mixing of drugs / Herbal formulations etc.
<b>HOSPITALS / HEALTHCARE / SCIENTIFIC RESEARCH LABS</b> Lab Glassware, Surgical Instruments, Syringes, Orthopedic Inserts, Eyeglass Frames, Dental Instruments, Dentures, etc. <b>DEFENCE</b> Army base workshops, Naval ships, Ship building centre for cleaning components and machinery parts. Airforce - aircraft components.	<b>ATOMIC RESEARCH LABS / NUCLEAR POWER STATIONS / SPACE RESEARCH CENTERS / RAILWAYS</b> Decontamination of radioactive components machinery parts, handling equipments and parts, critical components used in rocket launch vehicles, Ball Bearings, Axle Box, Workshop / Electrical components	<b>GENERAL INDUSTRIES</b> Filter Candles, Spinners, LPG Cylinder Valves, Spectacle frames, machine parts, motor cores, Leco filters, SS Bellows and flexible hoses, Kitchen equipments parts, cutlery brassware, Solar cells, investment castings, ceramic air jets, parts of gas chromatography, Ball point tips and refills, M.S. Sheet metal components etc.

#### 3.Drainage

15L ultrasonic cleaner is too heavy to pull out water by carrying whole machine up. So we have designed a drainage for you.

#### 4.Specification of JP-060S

<b>Model</b>	JP-060S	<b>Frequency</b>	40,000Hz
<b>Tank capacity</b>	15L	<b>Timer</b>	1-30 mins
<b>Tank size</b>	330*300*150mm	<b>Unit size</b>	387*325*280mm
<b>Box packing</b>	460*410*360 mm	<b>Function</b>	Degasing/Draining
<b>Ultrasonic power</b>	360W	<b>Heating power</b>	300W
<b>N.W.</b>	9.1kg	<b>G.W.</b>	10.3kg
<b>POWER SUPPLY</b>	AC 100 ~ 120V, 60Hz ; AC 220 ~ 240V, 50Hz		

#### 5. Other Recommendation

If tank size is not suitable for your spare parts, we have other big ultrasonic cleaner in store. And we can design and produce any special function ultrasonic cleaning machine you need.



JP-020S



3.2L



JP-040S



10L



JP-100S



30L

#### 6.SkyMen Advantage

We have been in this industry for 10 years and we are supplying machines to all seller all over the world.All distributor is welcome for win-win cooperation.

We have passes ISO,High Tech Company,CE,RoHS,FCC, National Medical Instrument Approval.

#### 7.Customers' feedback with skyMen cleaning machine

<https://www.youtube.com/watch?v=-VMzEqOlaXE>

[https://www.youtube.com/watch?v=cut8\\_HKLud8](https://www.youtube.com/watch?v=cut8_HKLud8)

Youtube: <https://www.youtube.com/watch?v=zjlppdkpLFw>

Youtube:<https://www.youtube.com/watch?v=oTHSCRt1H7Y&feature=youtu.be>



**SkyMen Technology Corporation Limited**



86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen